





General Information		
Series:	QFS	
Туре:	Flame Detection	
Style:	Connector	
Description:	Evaluation Kit	
Kit Contains:	USEQFS prototype flame sensing detector, sensors USEQFSEA50L180, USEQFSEA391180, USEQFSEA464180 and USEQFSEA448180, USB communications cable	
REACH	SVHC (PZT - CAS 12626-81-2)	
SCIP Number	f8c5f819-a3bd-41c4-887e-bd5dcb8c5edf	
Qualifications	REACH	
RoHS:	With Exemptions	

Packaging Specifications		
Packaging:	Cardboard Box	
Packaging Quantity:	1	
Weight:	350 g	

Specifications		
Temperature Range:	-40/+85°C	
Miscellaneous:	SMD flame sensing evaluation kit, including 4 QFS sensors	
Power Supply Voltage:	1.75 – 3.6 V	
Current:	1 – 23 μA (Supply Current Typical)	
D*:	2.5 x 10 ⁸ cm sqrt (Hz)/W	
NEP:	2.7 x 10 ⁻¹⁰ W/sqrt (Hz)	
Time Constant:	10 ms (10 – 20 Hz peak)	
Field of View:	90 degrees	
Element Size:	0.64 mm x 0.64 mm	
Filter Aperture:	d = 1.65 mm	

For additional sources of information, please refer to https://www.kemet.com/en/us/sensors/environmental-sensors.html