

# FOWX2.E356389 - FIXED CAPACITORS FOR USE IN ELECTRONIC EQUIPMENT - COMPONENT

## Fixed Capacitors for Use in Electronic Equipment - Component

See General Information for Fixed Capacitors for Use in Electronic Equipment - Component

### KEMET ELECTRONICS CORP

2835 Kemet Way  
Simpsonville, SC 29681-6202 USA

E356389

### Fixed Capacitors

Type Dsg	Capacitor Class	Voltage Rating (V)	Capacitance (μF) (Tolerance)@	Resistance for RC Devices (ohms)	Lower Temp (°C)	Upper Temp (°C)
KJN	X1	440 ac	8pF - 4700pF, +/-20%	—	-25	+125
	Y1	250/400 ac				
KJY	X1	400 ac	100pF - 10000pF, +/-20%	—	-25	+125
	Y2	250 ac				
ERP	X1/Y1	760 V ac, /	33pF ~4700pF,	—	-40	+125
		500 V ac	K(+/-10%), M(+/-20%)			
ERO	X1/Y2	440 V ac/	1000pF ~12000pF,	—	-40	+125
		250, 300 V ac	K(+/-10%), M(+/-20%)			
ERK	X1/Y2	440 V ac/	33pF ~4700pF,	—	-40	+125
		300 V ac	K(+/-10%), M(+/-20%)			
ERP	X1/Y1	760 V ac/	470pF ~4700pF,	—	-40	+125
		500 V ac	K(+/-10%), M(+/-20%)			
ERK	X1/Y2	440 V ac/	1000pF ~4700pF,	—	-40	+125

		300 V ac	K(+/-10%), M(+/-20%)			
C900 AH	X1	400 V ac	2-4700 pF/ +/-20%\$	—	-40	+125
	Y1	250/400 V ac				
C900 AC	X1	400/440 V ac	2-10000 pF/ +/-20%\$	—	-40	+125
	Y2	250/300 V ac				
C900 AS	X1	760 V ac	100-4700 pF/ +/-20%@	—	-40	+125
	Y1	500 V ac				
CAS17XXXXXXRGX &#	X2	250 ac	150~2200pF\$ +/-20%	—	-55	+125
CAS17XXXXXXRFX %#	X1/Y2	250 ac	100~1000pF\$ +/-20%	—	-55	+125
CAS26XXXXXXRFX %#	X1/Y2	250 ac	100~2700pF\$ +/-20%	—	-55	+125
CAS17XXXXXXGGX ^#	X2	250 ac	3~1000pF@ +/-20%	—	-55	+125
CAS18XXXXXXGGX ^#	X2	250 ac	10~1000pF! +/-20%	—	-55	+125
CAS18XXXXXXRGX &#	X2	250 ac	270~5600pF\$ +/-20%	—	-55	+125
CAS21XXXXXXRGX &#	X2	250 ac	10000~22000pF\$ +/-20%	—	-55	+125
CAS26XXXXXXGFX ##	X1/Y2	250 ac	4~100pF +/-20% (for impulse test 6KV)@ 4~680pF@ +/-20%	—	-55	+125
CAS18XXXXXXRFX %#	X1/Y2	250 ac	150~1000pF\$ +/-20%	—	-55	+125
CAS21XXXXXXRFX %#	X1/Y2	250 ac	160~4700pF\$ +/-20%	—	-55	+125
CAS17XXXXXXGFX ##	X1/Y2	250 ac	3~270pF@ +/-20%	—	-55	+125
CAS18XXXXXXGFX ##	X1/Y2	250 ac	10~470pF! +/-20%	—	-55	+125

Note \$: the model code may be followed by Tolerance M for +/-20%. K for +/-10%. J for +/-5%. D for +/-0.5PF. C for +/-0.25PF.

Note @: the model code may be followed by Tolerance M for +/-20%. K for +/-10%.


Note !: The model code may be followed by F for +/-1%, G for +/-2%, J for +/-5%, K for +/-10%, and M for +/-20%.

Note #: 1st X= C; 2nd-4th X= 1~9; 5th X= D, F, G, J, K, or M; 6th X= A; G= G; F=F; 7th X= CTU

Note % : 1st X= C; 2nd-4th X= 1~9; 5th X= D, F, G, J, K, or M; 6th X= A; R=R; F=F; 7th X= CTU.

Note ^ : 1st X= C; 2nd-4th X= 1~9; 5th X= D, F, G, J, K, or M; 6th X= A; G=G; G=G; 7th X= CTU.

Note & : 1st X= C; 2nd-4th X= 1~9; 5th X= D, F, G, J, K, or M; 6th X= A; R=R; G=G; 7th X= CTU.

Marking: Company name or trademark  and type designation.

Last Updated on 2019-02-25

---

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2019 UL LLC"