Axial Aluminum Electrolytic Capacitors

PEG126, +150°C

Built Into Tomorrow A4012 PEG126 • 8/8/2023

1

Overview

KEMET's PEG126 is an electrolytic capacitor with an outstanding electrical performance. The device has a polarized all-welded design, tinned copper wire leads, a negative pole connected to the case, and a plastic insulation. The PEG126 winding is housed in a cylindrical aluminum can with a high purity aluminum lid and a high quality rubber gasket. The low ESR is the result of a low resistive electrolyte/paper system and an all-welded design. Thanks to its mechanical robustness, the PEG126 is suitable for use in mobile and aircraft installations, with operation up to +150°C. KEMET's automotive grade capacitors meet the demanding Automotive Electronics Council's AEC-Q200 qualification requirements.

Applications

KEMET's PEG126 is a high performance axial electrolytic capacitor. It is designed for automotive applications, with high demands on resistance to vibrations and high ambient temperature.

Benefits

- · AEC-Q200 automotive qualified
- 2,000 hours at +150°C (D20 Case Size)
- · Resistance to vibrations
- · Resistance to high ambient temperature
- Low ESR
- High ripple capability
- · Polarized all-welded design
- · Outstanding electrical performance

Part Number System

PEG126	Н	F	368	E	Q	E1
Series	Rated Voltage (VDC)	Size Code	Capacitance Code (µF)	Version	Capacitance Tolerance	Packaging
Axial Aluminum Electrolytic	H = 25 K = 40 M = 63	See Dimension Table	The last two digits represent significant figures. The first digit indicates the total number digits.	E = Standard (with shrink tape)	Q = -10/+30% M = ±20%	E1 = Bulk





Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



Performance Characteristics

Item	Performance Characteristics					
Capacitance Range	250 – 4,000 μF					
Rated Voltage	25 - 63 VDC					
Operating Temperature	-40 to +150°C					
Capacitance Tolerance	-10/+30%, (±20% select values) at	100 Hz/+20°C				
	D (mm)	+125°C (hours)	+150°C (hours)			
Operational Lifetime	16 6,300		1,500			
	20	2,000				
Shelf Life	5,000 hours at +105°C or 10 years at +40°C 0 VDC					
	I = 0.003 CV + 4.0 (μA)					
Leakage Current	C = rated capacitance (μF), V = rated voltage (VDC). Voltage applied for 5 minutes at +20°C.					
	Proc	Requirements				
Vibration Test Specifications	1.5 mm displacement amplitude Vibration applied for three 2-hour s clamped	No leakage of electrolyte or other visible damage. Deviations in capacitance from initial measurements must not exceed: Δ C/C < 5%				
Standards	IEC 60384-4 long life grade 40/125/56, AEC-Q200					

Compensation Factor of Ripple Current (RC) vs. Frequency

Frequency	300 Hz	1 kHz	5 kHz	100 kHz
Coefficient	0.57	0.80	1.00	1.04

Test Method & Performance

Endurance Life Test						
Conditions	Performance					
Temperature	+150°C					
Test Duration	1,500 hours (D = 16 mm)					
Test Duration	2,000 hours (D = 20 mm)					
Ripple Current	Maximum ripple current specified in table					
Voltage	Voltage The sum of DC voltage and the peak AC voltage must not exceed the rated voltage of the capacitor					
Performance	The following specifications will be satisfied when the capacitor is tested at +20°C:					
Capacitance Change	Within 15% of the initial value					
Equivalent Series Resistance	Does not exceed 200% of the initial value					
Leakage Current Does not exceed leakage current limit						


Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



Ordering Options Table

Packaging Kind	Lead Length (mm)	Lead and Packaging Code						
S	Standard Packaging Option							
Bulk (box)	42 +3/-2	E1						

Dimensions - Millimeters



Size		Approximate					
Code	D	L	L1	d	LL	Weight	
oode	±0.5	±1	Minimum	±0.03	+3/-2	Grams	
F	16	29.0	35.0	1.0	42	8	
G	16	37.0	43.0	1.0	42	11	
Н	20	29.0	35.0	1.0	42	13	
J	20	37.0	43.0	1.0	42	20	
L	20	46.0	52.0	1.0	42	24	
Note: 11 is KEMET's recommendation for minimum distance between symmetrical lead bend. Available only for							

Note: L1 is KEMET's recommendation for minimum distance between symmetrical lead bend. Available only for customer specific part numbers. Lead bend dimensions must be specified and confirmed per article.

Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



Shelf Life

The capacitance, ESR and impedance of a capacitor will not change significantly after extended storage periods, however, the leakage current will very slowly increase. KEMET products are particularly stable and allow a shelf life in excess of ten years at 40°C. See sectional specification under each product for specific data.

Failure Rate

Estimated field failure rate: \leq 0.15 ppm (failures per year/produced number of capacitors per year). The expected failure rate for this capacitor range is based on field experience for capacitors with structural similarity.

Environmental Compliance

As an environmentally conscious company, KEMET is working continuously with improvements concerning the environmental effects of both our capacitors and their production. In Europe (RoHS Directive) and in some other geographical areas like China, legislation has been put in place to prevent the use of some hazardous materials, such as lead (Pb), in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products and fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material. KEMET will closely follow any changes in legislation world wide and make any necessary changes in its products, whenever needed.

Some customer segments such as medical, military and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products from each other, a special symbol is used on the packaging labels for RoHS compatible capacitors.

Due to customer requirements, there may appear additional markings such as lead-free (LF) or lead-free wires (LFW) on the label.

Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



Table 1 – Ratings & Part Number Reference

VDC	Rated Capacitance			Ripple Current Maximum			ESR Maximum		L _{ESL}	Part Number	
	100 Hz 20°С (µF)	Code	D x L (mm)	100 Hz 125°C (A)	≥ 5 kHz 105°C (A)	≥ 5 kHz 125°C (A)	≥ 5 kHz 150°C (A)	100 Hz 20°C (mΩ)	100 kHz 20°C (mΩ)	Approximate (nH)	
25	680	F	16 x 29	1.4	6.9	4.1	1.6	120	43	10	PEG126HF368EQE1
25	1000	G	16 x 37	1.7	8.8	5.2	2.0	80	28	12	PEG126HG410EQE1
25	1500	G	16 x 37	2.1	9.2	5.4	2.1	63	26	12	PEG126HG415EQE1
25	2200	Н	20 x 29	2.5	9.4	5.5	2.1	51	25	12	PEG126HH422EQE1
25	3300	J	20 x 37	3.2	11.7	6.9	2.6	34	17	15	PEG126HJ433EQE1
25	4000	L	20 x 46	3.7	13.1	7.7	2.9	29	14	17	PEG126HL440EME1
40	470	F	16 x 29	1.1	5.9	3.5	1.3	150	45	10	PEG126KF347EQE1
40	600	G	16 x 37	1.4	8.3	4.9	1.9	120	30	12	PEG126KG360EQE1
40	1000	н	20 x 29	1.9	9.4	5.5	2.1	75	23	12	PEG126KH410EQE1
40	1200	н	20 x 29	2.0	9.0	5.3	2.0	71	26	12	PEG126KH412EQE1
40	1500	н	20 x 29	2.2	9.7	5.7	2.2	58	22	12	PEG126KH415EQE1
40	2200	J	20 x 37	2.8	11.4	6.7	2.6	43	18	15	PEG126KJ422EQE1
40	2700	L	20 x 46	3.1	12.1	7.1	2.7	37	17	17	PEG126KL427EQE1
63	250	F	16 x 29	0.9	5.3	3.1	1.2	240	53	10	PEG126MF325EQE1
63	370	G	16 x 37	1.2	6.7	3.9	1.5	160	37	12	PEG126MG337EQE1
63	470	Н	20 x 29	1.4	7.3	4.3	1.6	130	32	12	PEG126MH347EQE1
63	680	J	20 x 37	1.7	9.0	5.3	2.0	90	23	15	PEG126MJ368EQE1
63	900	L	20 x 46	2.1	10.5	6.1	2.3	69	18	17	PEG126ML390EQE1
VDC	Rated Capacitance	Size Code	Case Size	Ripple Current		E	SR	L _{ESL}	Part Number		

Operational Life

Operational life (L_{op}) at ambient temperature T_a and ripple current I_{Acc} .

Diagram valid for 20 mm case size.


Operational life,

16 mm case size: 0.75 x diagram value

Example: Article: PEG126KJ422EQ (20 x 37 mm) Ambient temperature (T_a): +85°C Ripple current, at 10 kHz (I_{AC}): 12.0 A

 $I_{_{RAC}}$ (+125°C ≥ 5 kHz) = 6.7 A (from data table) $\rightarrow I_{_{AC}}/I_{_{RAC}}$ (+125°C) = 12.0/6.7 = 1.8

Operational life: Interpolation between the $\rm L_{_{op}}\text{-}curves \rightarrow \rm L_{_{op}} \sim 18 kh$ (blue curves)



Axial Aluminum Electrolytic Capacitors - PEG126, +150°C




Packaging Quantities

Size Code	Packaging Quantities Bulk			
F	125			
G	100			
н	150			
J	125			
L	100			

Marking



Construction



6

Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



Construction Data

The manufacturing process begins with the anode foil being electrochemically etched to increase the surface area and then "formed" to produce the aluminum oxide layer. Both the anode and cathode foils are then interleaved with absorbent paper and wound into a cylinder. During the winding process, aluminum tabs are attached to each foil to provide the electrical contact.

The winding is assembled to the capacitor Al-can and to the Al-lid. The can is filled with electrolyte and the winding is impregnated during a vacuum treatment. The capacitor is sealed. Throughout the process, all materials inside the housing must be maintained at the highest purity and be compatible with the electrolyte.

Each capacitor is aged and tested before being packed. The purpose of aging is to repair any damage in the oxide layer and thus reduce the leakage current to a very low level. Aging is carried out at elevated temperature and is accomplished by applying voltage to the device while carefully controlling the supply current. The process takes between 2 and 20 hours, depending on voltage rating.

Damage to the oxide layer can occur due to a variety of reasons:

- · Slitting of the anode foil after forming
- · Attaching the tabs to the anode foil
- Minor mechanical damage caused during winding


The following tests are applied for each individual capacitor.

Electrical:

- Leakage current
- Capacitance
- ESR
- Tan Delta

Mechanical/Visual:

- · Pull strength test of wire terminals
- Print detail
- Box labels
- Packaging, including packed quantity



Axial Aluminum Electrolytic Capacitors - PEG126, +150°C



KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET requires its products to be packaged and shipped on pallets. This is because KEMET's products are specifically designed to be packed onto pallets during shipment. If for any reason, the products are removed from pallets by the shipping party and shipped to the end customer, then additional external protection is required. In this instance, an external box with two carton layers and an upwards orientation sticker must be used by the shipping party, with the empty space filled with filling material, and afterwards sealing the box. If this packing and packaging guideline is not followed by the shipping party, the shipping party, and not KEMET, will be held responsible for any packaging, packing and/or product damages upon delivery of the products to the end customer. KEMET hereby disclaims any liability for damages to the products or otherwise that have been, or threaten to be, inflicted, result from or are in any way related to the packaging, packing or damage by the shipping party in contravention of the packaging guidelines herein.

KEMET is a registered trademark of KEMET Electronics Corporation.

8