# A957, +85°C, High Voltage









### **Overview**

KEMET's A957 is an electrolytic capacitor module with outstanding electrical performance and high ripple current. This device contains a bank of ALF70 Aluminum Electrolytic Capacitors mounted on high current designed PCB. These assembled parts are housed by a plastic case and heat sinked by a casted aluminum plate.

### **Benefits**

- Capacitor bank ready to fit into application
- · Eliminates the use of voltage sharing resistors
- · Capacitor Bank with heat-sink included
- Long life, up to 18,000 hours at +85°C (V<sub>p</sub>, I<sub>p</sub> applied)
- · Extremely high ripple current
- Low ESL
- Outstanding electrical performance

## **Applications**

The KEMET A957 is an electrolytic capacitor module, designed mainly for applications, like Solar Inverters, Motor Drives, and Pulsed Power.



# **Part Number System**

A	957	AL	132	M	800	S
Capacitor Class	Series	Size Code	Capacitance Code (µF)	Tolerance	Rated Voltage (VDC)	Termination
A = Aluminum	Aluminum Electrolytic Capacitor Module	See Dimension Table	First two digits represent significant figures. Third digit specifies number of zeros.	M = ±20%	700 = 700 V 800 = 800 V 900 = 900 V 1K0 = 1,000 V 1K1 = 1,100 V 1K2 = 1,200 V	S = Screw



## **Performance Characteristics**

Item	Performance Characteristics							
Capacitance Range	560 – 1,800 μF							
Rated Voltage	700 – 1,200 VDC							
Operating Temperature	-40 to +85°C	-40 to +85°C						
Storage Temperature Range	−55 to +85°C							
Capacitance Tolerance	±20% at 100 Hz/+20°C							
0	Rated Voltage and Ripple Current at +85°C (hours)	Rated Voltage at +85°C (hours)						
Operational Lifetime	18,000	29,000						
Shelf Life	2,000 hours at +85°C or 30,000 hours at +40°C 0 VDC							
Lackaga Current	I = 0.006 CV or 6,000 μA (whichever is smaller)							
Leakage Current	C = rated capacitance (μF), V = rated voltage (VDC). Voltage applied for 5 minutes at +20°C.							
	Procedure	Requirements						
Vibration Test Specifications	0.35 mm displacement amplitude or 5 G maximum acceleration. Vibration applied for three directions 0.5-hour sessions at 10 – 55 Hz. No leakage of electrolyte or other visible dam Deviations in capacitance from initial measure must not exceed $\Delta$ C/C ±5%							
Standards	Standards IEC 60384-4 long life grade 40/85/56							

# **Surge Voltage**

Test Condition	Voltage (VDC)							
≤ 30 second surge followed by a no	700	800	900	1,000	1,100	1,200		
load period of 330 seconds, 1,000 cycles at +85°C	770	880	990	1,100	1,210	1,320		


# **Test Method & Performance**

Endurance Life Test						
Conditions	Performance					
Temperature	+85°C					
Test Duration	2,000 hours					
Ripple Current	Rated ripple current specified in table					
Voltage	The sum of DC voltage and the peak AC voltage must not exceed the rated voltage of the capacitor					
Performance	The following specifications will be satisfied when the capacitor is tested at +20°C:					
Capacitance Change	Within 10% of the initial value					
Equivalent Series Resistance	Does not exceed 150% of the initial value					
Leakage Current	Does not exceed leakage current limit					




# **Dimensions - Millimeters**


### **Module Top View**



#### Module Side View



## PCB Top View (Without Capacitors)



Circ	Dimensions									Annuavimete		
Size Code	Α	Δ   R   C   D   F   F   G   H   I   I   W								Approximate Weight (g)		
	± 0.5	± 0.5	±0.1	± 0.5	± 0.5	± 0.5	±0.1	±0.5	±0.1	± 0.5	± 0.5	3 (3)
AL	18.0	92.0	42.5	7.0	114.4	121.4	67.4	96.1	19.0	141.4	110.0	669.3

Recommended Terminal Screws:

Slotted Head Hex Screw (M5 x 0.8, 10.0 mm length, 2.0 maximum torque) Socket Head Steel Screw (M5 x 0.8, 10.0 mm length, 6.0 maximum torque) Stainless Steel Washer should be used



#### **Shelf Life**

The capacitance, ESR and impedance of a capacitor will not change significantly after extended storage periods, however, the leakage current will very slowly increase. KEMET products are particularly stable and allow a shelf life in excess of three years at 40°C. See sectional specification under each product for specific data.

#### Re-Age (Reforming) Procedure

Apply the rated voltage to the capacitor at room temperature for a period of one hour, or until the leakage current has fallen to a steady value below the specified limit. During re-aging, a maximum charging current of twice the specified leakage current or 5 mA (whichever is greater) is suggested.

### Reliability

Estimated field failure rate:

Size Codes	Estimated field failure rate ≤ (ppm)*
AL	1.20

(\*Failures per year/produced number of capacitors per year)

The expected failure rate for this capacitor module range is based on field experience for single capacitors with structural similarity.

### **Environmental Compliance**







All Part Numbers in this datasheet are Reach and RoHS compliant and Halogen-Free.

As an environmentally conscious company, KEMET is working continuously with improvements concerning the environmental effects of both our capacitors and their production.

In Europe (RoHS Directive) and in some other geographical areas such as China, legislation has been put in place to prevent the use of some hazardous materials, such as lead (Pb), in electronic equipment. All products in this catalog are produced to help our customers' obligations to guarantee their products and fulfill these legislative requirements. The only material of concern in our products has been lead (Pb), which has been removed from all designs to fulfill the requirement of containing less than 0.1% of lead in any homogeneous material. KEMET will closely follow any changes in legislation world wide and makes any necessary changes in its products, whenever needed.

Some customer segments such as medical, military, and automotive electronics may still require the use of lead in electrode coatings. To clarify the situation and distinguish products from each other, a special symbol is used on the packaging labels for RoHS compatible capacitors.

Due to customer requirements, there may appear additional markings such as lead-free (LF) or lead-free wires (LFW) on the label.




# **Table 1 - Ratings & Part Number Reference**

Rated Voltage	Rated Capacitance	Size Code	Case Size	Ripple Current		* *		ESR Maximum	Impedance Maximum	Part Number
(VDC)	100 Hz 20°C (μF)		L x W x H (mm)	100 Hz 10 kHz 85°C 85°C (A) <sup>1</sup> (A) <sup>1</sup>		100 Hz 20°C (mΩ)	10 kHz 20°C (mΩ)			
700	1,800	AL	141.4 x 110.0 x 96.1	15.20	29.70	84	43	A957AL182M700S		
800	1,300	AL	141.4 x 110.0 x 96.1	13.20	27.20	114	66	A957AL132M800S		
900	1,000	AL	141.4 x 110.0 x 96.1	11.93	23.03	209	150	A957AL102M900S		
1,000	910	AL	141.4 x 110.0 x 96.1	10.46	15.87	484	421	A957AL911M1K0S		
1,100	620	AL	141.4 x 110.0 x 96.1	11.19	22.26	214	149	A957AL621M1K1S		
1,200	560	AL	141.4 x 110.0 x 96.1	10.65	21.64	241	166	A957AL561M1K2S		


<sup>&</sup>lt;sup>1</sup> Module ambient temperature

# **Marking**





### **Construction**







#### **Construction Data**

The manufacturing process begins with the anode foil being electrochemically etched to increase the surface area and then "formed" to produce the aluminum oxide layer. Both the anode and cathode foils are then interleaved with absorbent paper and wound into a cylinder. During the winding process, aluminum tabs are attached to each foil to provide the electrical contact.

The winding is assembled to the capacitor Al-can and to the Al-lid. The can is filled with electrolyte and the winding is impregnated during a vacuum treatment. The capacitor is sealed. Throughout the process, all materials inside the housing must be maintained at the highest purity and be compatible with the electrolyte.

Each capacitor is aged and tested before being packed. The purpose of aging is to repair any damage in the oxide layer and thus reduce the leakage current to a very low level. Aging is carried out at elevated temperature and is accomplished by applying voltage to the device while carefully controlling the supply current. The process takes between 2 and 20 hours, depending on voltage rating.

Damage to the oxide layer can occur due to a variety of reasons:

- Slitting of the anode foil after forming
- Attaching the tabs to the anode foil
- Minor mechanical damage caused during winding


The following tests are applied for each individual capacitor.


#### Electrical:

- Leakage current
- Capacitance
- ESR
- · Tan Delta

#### Mechanical/Visual:

- · Pull strength test of wire terminals
- · Print detail
- · Box labels
- · Packaging, including packed quantity







### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### **Disclaimer**

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET requires its products to be packaged and shipped on pallets. This is because KEMET's products are specifically designed to be packed onto pallets during shipment. If for any reason, the products are removed from pallets by the shipping party and shipped to the end customer, then additional external protection is required. In this instance, an external box with two carton layers and an upwards orientation sticker must be used by the shipping party, with the empty space filled with filling material, and afterwards sealing the box. If this packing and packaging guideline is not followed by the shipping party, the shipping party, and not KEMET, will be held responsible for any packaging, packing and/or product damages upon delivery of the products to the end customer. KEMET hereby disclaims any liability for damages to the products or otherwise that have been, or threaten to be, inflicted, result from or are in any way related to the packaging, packing or damage by the shipping party in contravention of the packaging guidelines herein.