SCR Series, Radial, C³ Technology, COG Dielectric, 50 - 200 VDC (Commercial Grade)



Overview

KEMET's radial through-hole ceramic SCR Series capacitors in COG dielectric feature proprietary Ceramic Cased Capacitor temperature and is considered "stable." The Electronics (C3) Technology and are designed to meet the needs of critical, high reliability and higher temperature applications. C³ Technology features a unique lead attach configuration with direct internal connection to the Multilayer Ceramic Capacitor (MLCC) electrode system. This configuration promotes superior "pull away" performance and uniform coefficient of linear expansion characteristics at elevated temperatures when compared to conventional through-hole technologies. Design details are outlined in U.S. Patent Number 4931899.

COG dielectric features a 125°C maximum operating Industries Alliance (EIA) characterizes COG dielectric as a Class I material. Components of this classification are temperature compensating and are suited for resonant circuit applications or those where Q and stability of capacitance characteristics are required. COG exhibits no change in capacitance with respect to time and voltage and boasts a negligible change in capacitance with reference to ambient temperature. Capacitance change is limited to ±30 ppm/°C from -55°C to +125°C.

Benefits

- Radial through-hole form factor
- Non-encapsulated
- Proprietary and robust C³ Technology design
- 0.200" and 0.400" lead spacing
- -55°C to +125°C operating temperature range
- DC voltage ratings of 50 V, 100 V and 200 V
- Capacitance offerings ranging from 10 pF up to 0.18 μF
- Available capacitance tolerances of ±5%, ±10% and ±20%



Ordering Information

S	C	R	09	D	184	J	W	S	
Specification/ Series	Dielectric	Lead Configuration	Style /Size	Rated Voltage (VDC)	Capacitance Code (pF)	Capacitance Tolerance ¹	Lead Finish ²	Screening Option	Packaging/ Grade (C-Spec)
S=Standard	C = COG	R =Radial	05 06 07 08 09	B = 50 D = 100 F = 200	Two significant digits and number of zeros Use 9 for 1.0 – 9.9 pF Use 8 for 0.5 – .99 pF ex. 2.2 pF = 229 ex. 0.5 pF = 508	J = ±5% K = ±10% M = ±20%	W = SnPb (60/40) G = Au	S = Standard A = Group A (MIL-PRF-20)	Blank = Tray


¹ Additional capacitance tolerance offerings may be available. Contact KEMET for details.

Standard: 60% tin (Sn)/40% lead (Pb) finish with 100% copper core ("C" designation). Alternative lead materials and finishes may be available. Contact KEMET for details.

² Lead materials:



Dimensions - Inches (Millimeters)



Series	Style/ Size	S Lead Spacing	L Length Maximum	H Height Maximum	T Thickness Maximum	LD Lead Diameter	LL Lead Length Minimum
	05	0.00.0.015	0.200 (5.08)	0.200 (5.08)	0.100 (2.54)	0.000.000	
	106	0.20±0.015 (5.08±0.38)	0.300 (7.62)	0.300 (7.62)	0.100 (2.54)	0.020±0.002 (0.508±0.051)	
SCR	07	(3.00±0.30)	0.300 (7.62)	0.300 (7.62)	0.150 (3.81)	(0.300±0.031)	1.25 (31.75)
	08	0.40±0.02	0.500 (12.70)	0.500 (12.70)	0.100 (2.54)	0.025±0.002	
	09	(10.16±0.51)	0.500 (12.70)	0.500 (12.70)	0.150 (3.81)	(0.635±0.051)	

Benefits cont'd

- · No piezoelectric noise
- · Extremely low ESR and ESL
- · High thermal stability
- High ripple current capability
- No capacitance change with respect to applied rated DC voltage
- Negligible capacitance change with respect to temperature from -55°C to +125°C
- · No capacitance decay with time
- · Non-polar device, minimizing installation concerns
- SnPb-coated lead finish (60/40)
- Gold-plated lead finish option available upon request (RoHS)

Applications

Typical applications include critical timing, tuning, circuits requiring low loss, circuits with pulse, high current, decoupling, bypass, filtering, transient voltage suppression, blocking and energy storage.

Qualification/Certification

Commercial Grade products are subject to internal qualification. Details regarding test methods and conditions are referenced in Table 2, Performance & Reliability.



Environmental Compliance

Devices with standard lead finish option of 60% tin (Sn)/40% lead (Pb) do not meet RoHS criteria. Devices with gold (AU) lead finish option are RoHS Compliant.

Electrical Parameters/Characteristics

Item	Parameters/Characteristics
Operating Temperature Range	-55°C to +125°C
Capacitance Change with Reference to +25°C and 0 VDC Applied (TCC)	±30 ppm/°C
Aging Rate (Maximum % Cap Loss/Decade Hour)	0%
Dielectric Withstanding Voltage	250% of rated voltage (5±1 second and charge/discharge not exceeding 50 mA)
Dissipation Factor (DF) Maximum Limit at 25°C	0.1%
Insulation Resistance (IR) Limit at 25°C	1,000 megohm microfarads or 100 GΩ (Rated voltage applied for 120±5 seconds at 25°C)

To obtain IR limit, divide $M\Omega$ - μ F value by the capacitance and compare to $G\Omega$ limit. Select the lower of the two limits. Capacitance and dissipation factor (DF) measured under the following conditions:

Note: When measuring capacitance it is important to ensure the set voltage level is held constant. The HP4284 and Agilent E4980 have a feature known as Automatic Level Control (ALC). The ALC feature should be switched to "ON."

Post Environmental Limits

High Temperature Life, Biased Humidity, Moisture Resistance						
Dielectric Rated DC Voltage Capacitance Value DF (%) Cap Shift						
COG	All	All	0.5	0.3% or ±0.25 pF		

¹ MHz ±100 kHz and 1.0 V $_{ms}$ ±0.2 V if capacitance \leq 1,000 pF 1 kHz ±50 Hz and 1.0 V $_{ms}$ ±0.2 V if capacitance > 1,000 pF



Table 1A - SCR05 Style/Size (0.200" Lead Spacing), Capacitance Range Waterfall

	SCR05 Sty	rle/Size (0.200" Lead \$	Spacing)	
Rated Voltage (VDC)		50	100	200
Voltag	e Code	В	D	F
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)		
10pF		100	100	100
12pF		120	120	120
15pF		150	150	150
18pF		180	180	180
22pF		220	220	220
27pF		270	270	270
33pF		330	330	330
39pF		390	390	390
47pF		470	470	470
56pF		560	560	560
68pF	_	680	680	680
82pF	_	820	820	820
100pF	_	101	101	101
120pF	_	121	121	121
150pF		151	151	151
180pF		181	181	181
220pF		221	221	221
270pF		271	271 331	271
330pF	J = ±5%	331 391	331	331
390pF	K = ±10% M = ±20%		471	391
470pF	IVI = 12U%	471		471
560pF	_	561 681	561 681	561 681
680pF 820pF	_	821	821	821
	_	102	102	102
1000pF		122	102	
1200pF			152	122
1500pF 1800pF		152 182	182	152 182
2200pF		222	222	222
2700pF		272	272	272
3300pF		332	332	332
2700pF		272	272	272
3300pF		332	332	332
3900pF		332	392	332
4700pF		472	472	472
5600pF		562	562	562
6800pF		682	682	302
8200pF		822	822	
0.01µF		103	103	
Rated Volt	ane (VDC)	50	100	200
Voltag	e Code	В	D	F



Table 1B - SCR06 Style/Size (0.200" Lead Spacing), Capacitance Range Waterfall

	SCR06 Sty	/le/Size (0.200" Lead	Spacing)	
Rated Voltage (VDC)		50	100	200
Voltag	e Code	В	D	F
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)		
330pF		331	331	331
390pF		391	391	391
470pF		471	471	471
560pF		561	561	561
680pF		681	681	681
820pF		821	821	821
1000pF		102	102	102
1200pF		122	122	122
1500pF		152	152	152
1800pF		182	182	182
2200pF		222	222	222
2700pF		272	272	272
3300pF	J = ±5%	332	332	332
2700pF	K = ±10%	272	272	272
3300pF	M = ±20%	332	332	332
3900pF		392	392	392
4700pF		472	472	472
5600pF		562	562	562
6800pF		682	682	682
8200pF		822	822	822
0.01µF		103	103	103
0.012µF		123	123	123
0.015µF		153	153	
0.018µF		183	183	
0.022µF		223	223	
0.027µF		273	273	
0.033µF		333	333	
Rated Vol	tage (VDC)	50	100	200
Voltag	e Code	В	D	F



Table 1C - SCR07 Style/Size (0.200" Lead Spacing), Capacitance Range Waterfall

SCR07 Style/Size (0.200" Lead Spacing)						
Rated Voltage (VDC)		50	100	200		
Voltag	e Code	В	D	F		
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)				
330pF		331	331	331		
390pF	<u> </u>	391	391	391		
470pF		471	471	471		
560pF		561	561	561		
680pF		681	681	681		
820pF		821	821	821		
1000pF		102	102	102		
1200pF		122	122	122		
1500pF		152	152	152		
1800pF		182	182	182		
2200pF		222	222	222		
2700pF		272	272	272		
3300pF		332	332	332		
2700pF		272	272	272		
3300pF	J = ±5%	332	332	332		
3900pF	K = ±10%	392	392	392		
4700pF	M = ±20%	472	472	472		
5600pF		562	562	562		
6800pF		682	682	682		
8200pF		822	822	822		
0.01µF		103	103	103		
0.012µF		123	123	123		
0.015µF		153	153	153		
0.018µF		183	183	183		
0.022µF		223	223			
0.027μF		273	273			
0.033µF		333	333			
0.039µF		393	393			
0.047µF		473	473			
0.056µF		563	563			
0.068µF		683	683			
Rated Vol	tage (VDC)	50	100	200		
Voltan	je Code	В	D	F		



Table 1D - SCR08 Style/Size (0.400" Lead Spacing), Capacitance Range Waterfall

SCR08 Style/Size (0.400" Lead Spacing)						
Rated Voltage (VDC) Voltage Code		50	100	200		
		В	D	F		
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)				
680pF		681	681	681		
820pF		821	821	821		
1000pF		102	102	102		
1200pF		122	122	122		
1500pF		152	152	152		
1800pF		182	182	182		
2200pF		222	222	222		
2700pF		272	272	272		
3300pF		332	332	332		
2700pF		272	272	272		
3300pF		332	332	332		
3900pF		392	392	392		
4700pF		472	472	472		
5600pF	J = ±5%	562	562	562		
6800pF	K = ±10%	682	682	682		
8200pF	M = ±20%	822	822	822		
0.01µF		103	103	103		
0.012µF		123	123	123		
0.015µF		153	153	153		
0.018µF		183	183	183		
0.022µF		223	223	223		
0.027µF		273	273	273		
0.033µF		333	333	333		
0.039µF		393	393	393		
0.047µF		473	473	473		
0.056µF		563	563	563		
0.068µF		683	683	683		
0.082µF		823	823			
0.1µF		104	104			
Rated Vol	tage (VDC)	50	100	200		
	je Code	В	D	F		



Table 1E - SCR09 Style/Size (0.400" Lead Spacing), Capacitance Range Waterfall

SCR09 Style/Size (0.400" Lead Spacing)						
Rated Vol	tage (VDC)	50	100	200		
Voltag	e Code	В	D	F		
Capacitance	Capacitance Tolerance	Capacitance Code (Available Capacitance)				
680pF		681	681	681		
820pF		821	821	821		
1000pF		102	102	102		
1200pF		122	122	122		
1500pF		152	152	152		
1800pF		182	182	182		
2200pF		222	222	222		
2700pF		272	272	272		
3300pF		332	332	332		
2700pF		272	272	272		
3300pF		332	332	332		
3900pF		392	392	392		
4700pF		472	472	472		
5600pF		562	562	562		
6800pF	1 150	682	682	682		
8200pF	J = ±5% K = ±10%	822	822	822		
0.01µF	M = ±20%	103	103	103		
0.012µF	IVI - 120 %	123	123	123		
0.015µF		153	153	153		
0.018µF		183	183	183		
0.022µF		223	223	223		
0.027µF		273	273	273		
0.033µF		333	333	333		
0.039µF		393	393	393		
0.047µF		473	473	473		
0.056µF		563	563	563		
0.068µF		683	683	683		
0.082µF		823	823			
0.1µF		104	104			
0.12µF		124	124			
0.15µF		154	154			
0.18µF		184	184			
Rated Vol	tage (VDC)	50	100	200		
Voltag	je Code	В	D	F		




Soldering Process

Recommended Soldering Technique:

- · Solder Wave
- Hand Soldering (Manual)


Recommended Soldering Profile:

· Optimum Wave Solder Profile



Hand Soldering (Manual)

Manual Solder Profile with Pre-heating



KEMET recommends following the guidelines and techniques outlined in technical bulletins F2103 and F9207.



Table 2 - Performance & Reliability: Test Methods and Conditions

Stress	Reference	Test or Inspection Method	
		Magnification 50 X. Conditions:	
0.11.139	J-STD-002	a) Method B, 4 hours at 155°C, dry heat at 235°C	
Solderability	J-51D-002	b) Method B at 215°C category 3	
		c) Method D, category 3 at 260°C	
Temperature Cycling	JESD22 Method JA-104	1,000 cycles (-55°C to +125°C), Measurement at 24 hours. +/-2 hours after test conclusion.	
5: 111 :15	MIL-STD-202 Method	Load Humidity: 1,000 hours 85°C/85% RH and Rated Voltage. Add 100 K ohm resistor. Measurement at 24 hours. +/-2 hours after test conclusion.	
Biased Humidity	103	Low Volt Humidity: 1,000 hours 85°C/85% RH and 1.5 V. Add 100 K ohm resistor. Measurement at 24 hours. +/-2 hours after test conclusion.	
Moisture Resistance	MIL-STD-202 Method 106	t = 24 hours/cycle. Steps 7a and 7b not required. Unpowered. Measurement at 24 hours. +/-2 hours after test conclusion.	
Thermal Shock	MIL-STD-202 Method 107	-55°C/+125°C. Note: Number of cycles required – 300. Maximum transfer time – 20 seconds. Dwell time – 15 minutes. Air – Air.	
High Temperature Life	MIL-STD-202 Method 108 /EIA-198	1,000 hours at 125°C (85°C for X5R, Z5U and Y5V) with 2 X rated voltage applied.	
Storage Life	MIL-STD-202 Method 108	150°C, 0 VDC, for 1,000 hours.	
Vibration	MIL-STD-202 Method 204	5 g for 20 minutes, 12 cycles each of 3 orientations. Note: Use 8"X5" PCB .031" thick 7 secure points on one long side and 2 secure points at corners of opposite sides. Parts mounted within 2" from any secure point. Test from 10 – 2,000 Hz.	
Resistance to Soldering Heat	MIL-STD-202 Method 210	Condition B. No pre-heat of samples. Note: single wave solder – procedure 2.	
Terminal Strength	MIL-STD-202 Method 211	Conditions A (2.3 kg or 5 lbs)	
Mechanical Shock	MIL-STD-202 Method 213	Figure 1 of Method 213, Condition F.	
Resistance to Solvents	MIL-STD-202 Method 215	Add aqueous wash chemical, OKEM Clean or equivalent.	

Storage & Handling

Ceramic chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature-reels may soften or warp, and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C, and maximum storage humidity not exceed 70% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts, and atmospheres should be free of chlorine and sulfur bearing compounds. For optimized solderability, chip stock should be used promptly, preferably within 1.5 years of receipt.



Packaging Details

Lead Spacing	Component Pitch (P1)
0.100 (2.54)	5.08
0.200 (5.08)	3.81
0.400 (10.16)	7.62
0.170 (4.32)	
0.220 (5.59)	
0.275 (6.98)	
0.300 (7.62)	
0.375 (9.52)	
0.475 (12.06)	
0.575 (14.60)	
0.675 (17.14)	

Packaging Quantities

Series	Style/Size	Tray Quantity Minimum ¹	Tray Quantity Maximum ¹
	05		56
	06		20
SCR	07	1	28
	08		20
	09		20

¹ Minimum order value applies. Contact KEMET for details.

Marking

Manufacturer's ID	KEC
Capacitance	106J
Voltage	50V
Date Code	123



KEMET Electronic Corporation Sales Offices

For a complete list of our global sales offices, please visit www.kemet.com/sales.

Disclaimer

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed.

All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicted or that other measures may not be required.