


#### **Overview**

The KEMET T428 was developed to provide the volumetric efficiency of a conformally coated capacitor in a pickand-place friendly molded package. The planerity of the molded package eliminates the "drops" associated with the conformally coated tantalum surface mount devices. This new package design offers the highest CV/cc of any molded leadframe product. In addition, the facedown construction offers higher power ratings per cc. The robust design features and testing protocol make this part suitable for application in the telecommunications, industrial, defense, and aerospace markets.

# **Benefits**

- High CV/cc
- Tape & Reel standard packaging per EIA 481
- Laser-marked case
- 100% surge current test available
- Extended range values
- Pick-and-place friendly



# **Applications**

Typical applications include decoupling and filtering in telecommunications, computer, industrial, defense, and aerospace applications.

#### **Environmental Compliance**

RoHS Compliant when ordered with 100% Sn or Ni-Pd-Au.

- Halogen-free
- Epoxy compliant with UL94 V-0
- Molded Epoxy complies for outgassing testing under ASTM E 595.



#### K-SIM

For a detailed analysis of specific part numbers, please visit ksim.kemet.com to access KEMET's K-SIM software. KEMET K-SIM is designed to simulate behavior of components with respect to frequency, ambient temperature, and DC bias levels.

### **Ordering Information**

Т	428	Ρ	337	K	010	Α	Н	61	10
Capacitor Class	Series	Case Size	Capacitance Code (pF)	Capacitance Tolerance	Rated Voltage (VDC)	Failure Rate/ Design	Termination Finish	Surge	ESR
T = Tantalum	High volumetric efficiency facedown Hi-Rel MnO <sub>2</sub> COTS	Ρ	First two digits represent significant figures. Third digit specifies number of zeros.	J = ±5% K = ±10% M = ±20%	004 = 4 006 = 6.3 010 = 10 016 = 16 020 = 20 025 = 25 035 = 35 050 = 50	A = N/A B = 0.1%/ 1,000 hours	H = Standard solder-coated (SnPb 5% Pb)	61 = None 62 = 10 cycles, 25°C 63 = 10 cycles, -55°C and 85°C	10 = Standard 20 = Low 30 = Ultra-low

# **Performance Characteristics**

Item	Performance Characteristics		
Operating Temperature	-55°C to 125°C		
Rated Capacitance Range	15 – 470 μF at 120 Hz/25°C		
Capacitance Tolerance	J Tolerance (5%), K Tolerance (10%), M Tolerance (20%)		
Rated Voltage Range	4 – 50 V		
DF (120 Hz)	Refer to Part Number Electrical Specification Table		
ESR (100 kHz)	Refer to Part Number Electrical Specification Table		
Leakage Current	$\leq$ 0.01 CV (µA) at rated voltage after 5 minutes		



# Qualification

Test	Condition			Charac	teristics			
			ΔC/C	Within ±10%	6 of initial valu	e		
Endurance	85°C at rated voltage, 2,000 hours	DF	Within initia	al limits				
Endurance	125°C at 2/3 rated voltage, 2,000 hours		DCL	Within 1.25	x initial limit			
			ΔC/C	Within ±10%	6 of initial valu	e		
Otorono Life	Storogo Life 125°C at 0 volto 2 000 hours				al limits			
Storage Life	125°C at 0 volts, 2,000 hours		DCL	Within 1.25	x initial limit			
					al limits			
					of initial value			
Thermal Shock	MIL-STD-202, Method 107, Condition B, mo	DF	Within initial limits					
I nermai Shock	-55°C to 125°C, 1,000 cycles	DCL	Within 1.25 x initial limit					
					Within initial limits			
		+25°C	-55°C	+85°C	+125°C			
Tanan anatana Otakilita	Extreme temperature exposure at a	ΔC/C	IL*	±10%	±10%	±20%		
Temperature Stability	succession of continuous steps at +25°C, -55°C, +25°C, +85°C, +125°C, +25°C	DF	IL	IL	1.5 x IL	1.5 x IL		
		DCL	IL	n/a	10 x IL	12 x IL		
			ΔC/C	Within ±5%	of initial value	<u>.</u>		
Ourse Maltana	85°C, 1.32 x rated voltage 1,000 cycles		DF	Within initia	al limits			
Surge Voltage	(125°C, 1.2 x rated voltage)		DCL	Within initia	Within initial limits			
			ESR	Within initial limits				
	MIL-STD-202, Method 213, Condition I, 100	G neak	ΔC/C	Within ±10	of initial value			
Mechanical Shock/ Vibration	MIL-STD-202, Method 204, Condition D, 10		DF	Within initial limits				
Vibration	2,000 Hz, 20 G peak		DCL	Within initial limits				
Additional Qualification Tests per MIL-PRF- 55365/8	Please contact KEMET for more information							


\*IL = Initial limit

# Certification

MIL-PRF-55365/8




## **Electrical Characteristics**




#### Impedance & ESR vs. Frequency







#### **Dimensions – Millimeters**



Case Size	Component								
EIA	L Max	W ±0.3	H ±0.3	F ±0.20	S ±0.20	A (Nom)	(mg)		
7360-38	7.2	6.0	3.5	4.95	1.6	3.8	62.6		

These weights are provided as reference. If exact weights are needed, please contact your KEMET Sales Representative

### Table 1 – Ratings & Part Number Reference

Rated Voltage	Rated Cap	Case Code/ Case Size	KEMET Part Number	DC Leakage	DF	Standard ESR	Low ESR	Ultra- Low ESR	Ripple Current (rms)	Maximum Operating Temp	MSL
VDC at 85°C	μF	KEMET/EIA	(See below for part options)	µA at +25°C Maximum/ 5 Minutes	% at +25°C 120 Hz Maximum	mΩ at +25°C 100 kHz Maximum	mΩ at +25°C 100 kHz Maximum	Ω at +25°C 100 kHz Maximum	mA at +25°C 100 kHz	°C	Reflow Temp. ≤ 260°C
4	470	P/7360-38	T428P477(1)004(2)(3)(4)(5)	18.8	10.0	130	45	NA	2,687	125	1
6.3	390	P/7360-38	T428P397(1)006(2)(3)(4)(5)	24.6	8.0	130	45	NA	2,687	125	1
6.3	470	P/7360-38	T428P477(1)006(2)(3)(4)(5)	29.6	10.0	120	50	NA	2,550	125	1
10	330	P/7360-38	T428P337(1)010(2)(3)(4)(5)	33.0	8.0	130	45	NA	2,687	125	1
16	180	P/7360-38	T428P187(1)016(2)(3)(4)(5)	28.8	8.0	130	55	NA	2,430	125	1
16	220	P/7360-38	T428P227(1)016(2)(3)(4)(5)	35.2	8.0	120	55	NA	2,430	125	1
20	150	P/7360-38	T428P157(1)020(2)(3)(4)(5)	30.0	8.0	140	100	NA	1,803	125	1
25	68	P/7360-38	T428P686(1)025(2)(3)(4)(5)	17.0	6.0	200	95	NA	1,850	125	1
35	22	P/7360-38	T428P226(1)035(2)(3)(4)(5)	7.7	6.0	280	220	NA	1,215	125	1
50	15	P/7360-38	T428P156(1)050(2)(3)(4)(5)	7.5	6.0	400	350	NA	964	125	1

(1) To complete KEMET part number, insert M for ±20%, K for ±10% or J for ±5%. Designates capacitance tolerance.

(2) To complete KEMET part number, insert B (0.1%/1,000 hours) or A = N/A.

(3) To complete KEMET part number, insert H = Solder-plated. Designates termination finish.

(4) To complete KEMET part number, insert 61 = none, 62 = 10 cycles +25°C, 63 = 10 cycles -55°C +85°C after Weibull or 64 = 10 cycles -55°C +85°C before Weibull. Designates surge current option.


(5) To complete KEMET part number, insert 10 = standard, 20 = ILow or 30 = ultra-low. Designates ESR option.

Please refer to Ordering Information for additional details.



### **Recommended Voltage Derating Guidelines**

	-55°C to 85°C	85°C to 125°C
% Change in Working DC Voltage with Temperature	V <sub>R</sub>	67% of $V_{R}$
Recommended Maximum Application Voltage	50% of $V_{\rm R}$	33% of $V_{\rm R}$



### **Ripple Current/Ripple Voltage**

Permissible AC ripple voltage and current are related to equivalent series resistance (ESR) and the power dissipation capabilities of the device. Permissible AC ripple voltage which may be applied is limited by two criteria:

1. The positive peak AC voltage plus the DC bias voltage, if any, must not exceed the DC voltage rating of the capacitor.

2. The negative peak AC voltage in combination with bias voltage, if any, must not exceed the allowable limits specified for reverse voltage. See the Reverse Voltage section for allowable limits.

The maximum power dissipation by case size can be determined using the table at right. The maximum power dissipation rating stated in the table must be reduced with increasing environmental operating temperatures. Refer to the table below for temperature compensation requirements.

Temperature Compensation Multipliers for Maximum Ripple Current							
T ≤ 25°C	T ≤ 85°C	T ≤ 125°C					
1.00 0.90 0.40							

T= Environmental Temperature

The maximum power dissipation rating must be reduced with increasing environmental operating temperatures. Refer to the Temperature Compensation Multiplier table for details

Case Code	EIA Case Code	Maximum Power Dissipation (Pmax) mWatts at 25°C with +20°C Rise
Р	7360-38	325

Using the Pmax of the device, the maximum allowable rms ripple current or voltage may be determined.

I(max) = √Pmax/R E(max) = Z √Pmax/R

I = rms ripple current (amperes) E = rms ripple voltage (volts) Pmax = maximum power dissipation (watts) R = ESR at specified frequency (ohms) Z = Impedance at specified frequency (ohms)



#### **Reverse Voltage**

Solid tantalum capacitors are polar devices and may be permanently damaged or destroyed if connected with the wrong polarity. The positive terminal is identified on the capacitor body by a stripe, plus in some cases a beveled edge. A small degree of transient reverse voltage is permissible for short periods per the below table. The capacitors should not be operated continuously in reverse mode, even within these limits.


Temperature	Permissible Transient Reverse Voltage
25°C	15% of Rated Voltage
85°C	5% of Rated Voltage
125°C	1% of Rated Voltage

### Table 2 - Land Dimensions/Courtyard

KEMET	Metric Size Code	I		sity Lev mum (I rotrusic	Nost)	)	Density Level B: Median (Nominal) Land Protrusion (mm)			Density Level C: Minimum (Least) Land Protrusion (mm)						
Case	EIA	X	Y	C	V1	V2	X	X Y C V1 V2			X	Y	C	V1	V2	
Р	7360-38	5.25	1.80	2.35	8.50	7.30	5.15	1.70	2.35	8.00	6.80	5.05	1.60	2.35	7.70	6.50

**Density Level A:** For low-density product applications. Recommended for wave solder applications and provides a wider process window for reflow solder processes.

**Density Level B:** For products with a moderate level of component density. Provides a robust solder attachment condition for reflow solder processes. **Density Level C:** For high component density product applications. Before adapting the minimum land pattern variations the user should perform qualification testing based on the conditions outlined in IPC Standard 7351 (IPC-7351).





## **Soldering Process**

KEMET's families of surface mount capacitors are compatible with wave (single or dual), convection, IR, or vapor phase reflow techniques. Preheating of these components is recommended to avoid extreme thermal stress. KEMET's recommended profile conditions for convection and IR reflow reflect the profile conditions of the IPC/J-STD-020D standard for moisture sensitivity testing. The devices can safely withstand a maximum of three reflow passes at these conditions.

Please note that although the X/7343-43 case size can withstand wave soldering, the tall profile (4.3 mm maximum) dictates care in wave process development.


Hand soldering should be performed with care due to the difficulty in process control. If performed, care should be taken to avoid contact of the soldering iron to the molded case. The iron should be used to heat the solder pad, applying solder between the pad and the termination, until reflow occurs. Once reflow occurs, the iron should be removed immediately. "Wiping" the edges of a chip and heating the top surface is not recommended.

During typical reflow operations, a slight darkening of the gold-colored epoxy may be observed. This slight darkening is normal and not harmful to the product. Marking permanency is not affected by this change.

Profile Feature	SnPb Assembly	Pb-Free Assembly
Preheat/Soak		
Temperature Minimum (T <sub>Smin</sub> )	100°C	150°C
Temperature Maximum (T <sub>Smax</sub> )	150°C	200°C
Time ( $t_s$ ) from $T_{smin}$ to $T_{smax}$ )	60 – 120 seconds	60 – 120 seconds
Ramp-up Rate ( $T_L$ to $T_P$ )	3°C/seconds maximum	3°C/seconds maximum
Liquidous Temperature $(T_L)$	183°C	217°C
Time Above Liquidous $(t_L)$	60 – 150 seconds	60 – 150 seconds
Peak Temperature (T <sub>P</sub> )	220°C* 235°C**	250°C* 260°C**
Time within 5°C of Maximum Peak Temperature (t <sub>P</sub> )	20 seconds maximum	30 seconds maximum
Ramp-down Rate $(T_P \text{ to } T_L)$	6°C/seconds maximum	6°C/seconds maximum
Time 25°C to Peak Temperature	6 minutes maximum	8 minutes maximum

Note: All temperatures refer to the center of the package, measured on the package body surface that is facing up during assembly reflow. \* For Case Size height > 2.5 mm \*\* For Case Size height < 2.5 mm

\*\* For Case Size height ≤ 2.5 mm




#### Storage


Tantalum chip capacitors should be stored in normal working environments. While the chips themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage. In addition, packaging materials will be degraded by high temperature – reels may soften or warp and tape peel force may increase. KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 60% relative humidity. Temperature fluctuations should be minimized to avoid condensation on the parts and atmospheres should be free of chlorine and sulphur bearing compounds. For optimized solderability chip stock should be used promptly, preferably within three years of receipt.



#### Construction




**Capacitor Marking** 





### **Tape & Reel Packaging Information**

KEMET's molded chip capacitor families are packaged in 8 and 12 mm plastic tape on 7" and 13" reels in accordance with *EIA Standard 481*: Embossed Carrier Taping of Surface Mount Components for Automatic Handling. This packaging system is compatible with all tape-fed automatic pick-and-place systems.




# Table 3 – Packaging Quantity

Case	Case Code		7" Reel*	13" Reel*
KEMET	EIA			
S	3216-12	8	2,500	10,000
Т	3528-12	8	2,500	10,000
М	3528-15	8	2,500	8,000
U	6032-15	12	1,000	5,000
L	6032-19	12	1,000	3,000
W	7343-15	12	1,000	3,000
Z	7343-17	12	1,000	3,000
V	7343-20	12	1,000	3,000
А	3216-18	8	2,000	9,000
В	3528-21	8	2,000	8,000
С	6032-28	12	500	3,000
D	7343-31	12	500	2,500
Q	7343-12	12	1,000	3,000
Y	7343-40	12	500	2,000
Х	7343-43	12	500	2,000
E/T428P	7360-38	12	500	2,000
Н	7360-20	12	1,000	2,500
0	7360-43	12	250	1,000

\* No C-Spec required for 7" reel packaging. C-7280 required for 13" reel packaging.



# Figure 1 – Embossed (Plastic) Carrier Tape Dimensions



# Table 4 – Embossed (Plastic) Carrier Tape Dimensions

#### Metric will govern

Constant Dimensions — Millimeters (Inches)									
Tape Size	D <sub>o</sub>	D <sub>1</sub> Minimum Note 1	E <sub>1</sub>	P <sub>0</sub>	P <sub>2</sub>	R Reference Note 2	S <sub>1</sub> Minimum Note 3	T Maximum	T <sub>1</sub> Maximum
8 mm	1.5 +0.10/-0.0 (0.059 +0.004/-0.0)	1.0 (0.039)	1.75 ±0.10 (0.069 ±0.004)	4.0 ±0.10 (0.157 ±0.004)	2.0 ±0.05 (0.079 ±0.002)	25.0 (0.984)	0.600 (0.024)	0.600 (0.024)	0.100 (0.004)
12 mm		1.5 (0.059)				30 (1.181)			

Variable Dimensions – Millimeters (Inches)									
Tape Size	Pitch	B <sub>1</sub> Maximum Note 4	E <sub>2</sub> Minimum	F	P <sub>1</sub>	T <sub>2</sub> Maximum	W Maximum	A <sub>0</sub> , B <sub>0</sub> & K <sub>0</sub>	
8 mm	Single (4 mm)	4.35 (0.171)	6.25 (0.246)	3.5 ±0.05 (0.138 ±0.002)	4.0 ±0.10 (0.157 ±0.004)	2.5 (0.098)	8.3 (0.327)		
12 mm	Single (4 mm) and Double (8 mm)	8.2 (0.323)	10.25 (0.404)	5.5 ±0.05 (0.217 ±0.002)	8.0 ±0.10 (0.315 ±0.004)	4.6 (0.181)	12.3 (0.484)	Note 5	

1. The embossment hole location shall be measured from the sprocket hole controlling the location of the embossment. Dimensions of embossment location and hole location shall be applied independent of each other.

2. The tape, with or without components, shall pass around R without damage (see Figure 4).

3. If  $S_1 < 1.0$  mm, there may not be enough area for cover tape to be properly applied (see EIA Standard 481–D, paragraph 4.3, section b).

4. B, dimension is a reference dimension for tape feeder clearance only.

5. The cavity defined by  $A_{\alpha}$ ,  $B_{\alpha}$  and  $K_{\alpha}$  shall surround the component with sufficient clearance that:

(a) the component does not protrude above the top surface of the carrier tape.

(b) the component can be removed from the cavity in a vertical direction without mechanical restriction, after the top cover tape has been removed.

(c) rotation of the component is limited to 20° maximum for 8 and 12 mm tapes (see Figure 2).

(d) lateral movement of the component is restricted to 0.5 mm maximum for 8 mm and 12 mm wide tape (see Figure 3).

(e) see Addendum in EIA Standard 481–D for standards relating to more precise taping requirements.



### **Packaging Information Performance Notes**


- 1. Cover tape break force: 1.0 kg minimum.
- 2. Cover tape peel strength: The total peel strength of the cover tape from the carrier tape shall be:

Tape Width	Peel Strength			
8 mm	0.1 to 1.0 newton (10 to 100 gf)			
12 mm	0.1 to 1.3 newton (10 to 130 gf)			


The direction of the pull shall be opposite the direction of the carrier tape travel. The pull angle of the carrier tape shall be  $165^{\circ}$  to  $180^{\circ}$  from the plane of the carrier tape. During peeling, the carrier and/or cover tape shall be pulled at a velocity of  $300 \pm 10$  mm/minute.

**3. Labeling:** Bar code labeling (standard or custom) shall be on the side of the reel opposite the sprocket holes. *Refer to EIA Standards 556 and 624*.


#### Figure 2 – Maximum Component Rotation



# Figure 3 – Maximum Lateral Movement




# Figure 4 – Bending Radius





# **Figure 5 – Reel Dimensions**



Note: Drive spokes optional; if used, dimensions B and D shall apply.


# Table 5 – Reel Dimensions

Metric will govern

Constant Dimensions — Millimeters (Inches)									
Tape Size	А	B Minimum	С	D Minimum					
8 mm	178 ±0.20								
12 mm	(7.008 ±0.008) or 330 ±0.20 (13.000 ±0.008)	1.5 (0.059)	13.0 +0.5/-0.2 (0.521 +0.02/-0.008)	20.2 (0.795)					
	Variable Dimensions – Millimeters (Inches)								
Tape Size	N Minimum	W <sub>1</sub>	W <sub>2</sub> Maximum	W <sub>3</sub>					
8 mm	50	8.4 +1.5/-0.0 (0.331 +0.059/-0.0)	14.4 (0.567)	Shall accommodate tape					
12 mm	(1.969)	12.4 +2.0/-0.0 (0.488 +0.078/-0.0)	18.4 (0.724)	width without interference					



# Figure 6 – Tape Leader & Trailer Dimensions



# Figure 7 – Maximum Camber





#### **KEMET Electronics Corporation Sales Offices**

For a complete list of our global sales offices, please visit www.kemet.com/sales.

#### Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

KEMET is a registered trademark of KEMET Electronics Corporation.