

EC系列 - 聚合物封装铂电阻温度传感器


温度范围 -50 °C至 +260 °C

性能特征

- 柔性氟碳外壳
- 防护等级IP69H
- 卓越的抗振动和抗冲击性能
- 高介电强度
- 符合DIN EN IEC 60751

应用示例

- 电动车的电机
- 工业力矩电机
- 充电站和插座
- 分析仪器
- 暖通空调



图片仅供参考

尺寸和材料

编号	产品类型	芯片电阻 R_0 [Ω]	尺寸和公差 (mm)				导线			产品料号
			HL	D	CL	L	线芯 (AWG)	绝缘	颜色	
1	EC3032-C	Pt100 / F 0.3	30 ± 5	3.2 $+0.2 -0.4$	400 ± 10	408 ± 10	24/19 NPC	PTFE	红色	5180937
2	EC3032-C	Pt1000 / F 0.3	30 ± 5	3.2 $+0.2 -0.4$	397 ± 10	405 ± 10	24/19 NPC	PTFE	红色	5016951
3	EC3032-C 车规级	Pt1000 / F 0.3	30 ± 5	3.2 $+0.2 -0.4$	400 ± 10	408 ± 10	24/19 NPC	PTFE	红色	5161009
4	EC3021-C	Pt1000 / F 0.3	30 ± 5	2.1 $+0.1 -0.4$	250 ± 10	258 ± 10	30/07 NPC	PTFE	蓝色	5185633
5	EC3021-C	Pt100 / F 0.3	30 ± 5	2.1 $+0.1 -0.4$	250 ± 10	258 ± 10	30/07 NPC	PTFE	蓝色	5185634

EC系列 - 聚合物封装铂电阻温度传感器

温度范围 -50 °C至 +260 °C

性能数据

编号	温度范围	介电强度AC (外壳)	响应时间 水流 (v = 0.4 m/s)		拉力 [N]	导体电阻 [Ω/m]	应用
			T0.5 [s]	T0.9 [s]			
1	-50 °C 至 +200 °C	6 kV / 60 s	3.1	8.1	> 50	0.081 ±10 %	多用途
2	-50 °C 至 +200 °C	6 kV / 60 s	3.1	8.1	> 50	0.081 ±10 %	多用途
3	-50 °C 至 +200 °C	6 kV / 60 s	3.1	8.1	> 50	0.081 ±10 %	汽车
4	-50 °C 至 +260 °C	3 kV / 60 s	1.8	4.8	> 25	0.32 ±10 %	多用途
5	-50 °C 至 +260 °C	3 kV / 60 s	1.8	4.8	> 25	0.32 ±10 %	多用途
6	-50 °C 至 +200 °C	6 kV / 60 s	3.1	8.1	> 50	0.081 ±10 %	多用途

温度系数

TCR = 3850 ppm/K

工作电流

Pt100 Ω: 0.3 至 1.0 mA

Pt1000 Ω: 0.1 至 0.3 mA

(必须考虑自加热)

自热系数 (元件)

0 °C 下 0.4K/mW

自定义选项

- 所有外部尺寸
- 导线尺寸和材质
- 传感器电阻值
- 连接器
- 认证 (如IMDS、PPAP、IP防水等级)

如需了解更多信息，
请浏览我们的传感器学
院！



IP69H
compliant

RoHS
compliant

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under www.yageo-nexensos.com/tc or may be furnished upon request. This data sheet is subject to changes without prior notice.