

## LS219, Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -50 °C to +150 °C

- Designed for low temperature applications
- Optimized for soldering connection
- High accuracy and interchangeability
- Excellent long term stability and low drift

LS series Pt-RTDs are designed for high volume low temperature applications where long term stability, interchangeability and accuracy are vital. Typical applications include HVAC, Food and Beverage, Medical and Industrial equipment.

Nominal Resistance $R_0$ [Ω]	Tolerance Class	Order Number	Packaging
Pt100	F 0.3 (B)	5205115	VCI-Plastic bag
Pt1000	F 0.3 (B)	5203377	VCI-Plastic bag

The measuring point for the nominal resistance is 2 mm from the end of the sensor body.

### Temperature Range of Tolerance Class

Validity of Class F 0.3 (B) -50 °C to +150 °C  
The specified tolerance classes refer to continuous operation.  
Short term temperature exposure for soldering: Max. 5 minutes up to 250 °C.

### Temperature Coefficient

TCR = 3850 ppm/K

### Response Time

Air ( $v = 3 \text{ m/s}$ ):  
 $t_{0.5} = 1.5 \text{ s}$   
 $t_{0.9} = 5 \text{ s}$

### Measuring Current

Pt100 Ω: 0.3 to 1 mA  
Pt1000 Ω: 0.1 to 0.3 mA  
(self-heating has to be considered)




Image for illustration purposes only  
Color, shape and forming of fixing drop may vary  
W2 only valid at outlet spot of wire

## LS219, Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -50 °C to +150 °C

### Long-Term Stability

The drift of the resistance value at 0 °C after a storage for 1000 hours in air at the declared upper temperature limit is not more than the tolerance value of the declared tolerance class according DIN EN IEC 60751.

Typical drift of R(0 °C) is <0.04 % after 1000 hours at +150 °C.

### Self-Heating

0.03 K/mW (Pt1000; Water v= 0,4m/s)

### Insulation Resistance

> 100 MΩ at +20 °C

### Connection Technology

Crimping, Soft Soldering

### Lead Type

Ni-silvercoated

### Tensile Strength of Leads

≥ 10 N

### Packaging

VCI-Plastic bag

Alternative packaging forms on request.

### Storage Life

At least 12 months (after manufacture), when stored under the recommended conditions. Longer shelf life may be possible, depending upon actual storage conditions, after requalification by customer. Nitrogen atmosphere recommended.

### Note

Other tolerances, values of resistance and wire lengths are available on request.

Due to random sample measurements, a bending of connection wires may occur (called V-shape). This bending is batch-dependent and has no influence on the functionality of the platinum measuring resistor.

### California Proposition 65



## WARNING

WARNING: This product can expose you to chemicals including nickel and cobalt, which are known to the State of California to cause cancer.

For more information go to [www.p65warnings.ca.gov](http://www.p65warnings.ca.gov)



The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under [www.yageo-nexensos.com/tc](http://www.yageo-nexensos.com/tc) or may be furnished upon request. This data sheet is subject to changes without prior notice.

YAGEO Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany

YAGEO Nexensos GmbH, Germany  
Web: [www.yageo-nexensos.com](http://www.yageo-nexensos.com)  
Contact: [nexensos.america@yageo.com](mailto:nexensos.america@yageo.com)

Document: 10000002962 Part 001 Version 00 | Status: 03/2025

Page 2 of 2