

M310 Automotive, 符合DIN EN IEC 60751的铂电阻温度传感器

温度范围-70 °C 至+500 °C, 可偶尔使用至+550 °C

- 车规级
- 适用于小直径设计环境的尺寸
- 出色的长期稳定性和低阻值漂移
- 高精度和易更换性
- 抗振动和抗冲击性
- 优化电阻焊, 钎焊, 压接的可连接性/提升连接稳定性

M系列薄膜铂电阻温度传感器具有长期稳定性和在宽工作温度范围内的保持高精度性能的特点. M310芯片结合了M系列的优点, 具有十分紧凑和小巧的尺寸, 适合小型测温探头或组件的安装. YAGEO Nexensos将根据客户的要求进行检查是否能满足其他要求(例如IMDS、PPAP).

标称阻值 R_0 [Ω]	公差等级	产品料号	包装方式
Pt1000	F 0.3 (B)	5185613	真空塑料包装

标称电阻测量点距离传感器本体末端 5 mm

公差等级及温度范围

公差等级 F 0.3 (B) -70 °C 至 +500 °C
规定的公差等级适用于连续运行状况下.
F 0.3 级也短时间适用于高达+550°C 温度下.

电阻温度系数


TCR = 3850 ppm/K

响应时间

水流 ($v = 0,4$ m/s): $t_{0.5} = 0.03$ s
 $t_{0.9} = 0.09$ s
气流 ($v = 3,0$ m/s): $t_{0.5} = 1.5$ s
 $t_{0.9} = 4.5$ s

工作电流

Pt1000 Ω : 0.1 to 0.3 mA
(必须考虑自加热)



图片仅供参考

固定滴的颜色, 形状与外观可能有所不同

W2尺寸仅适用于芯片引出导线处

M310 Automotive, 符合DIN EN IEC 60751的铂电阻温度传感器

温度范围-70 °C 至+500 °C, 可偶尔使用至+550 °C

长期稳定性

在规定的温度上限下使用 1000 小时后 0 °C 下的阻值漂移不超过 DIN EN IEC 60751 的公差等级公差。

在 500 °C 下 1000 小时后, R (0 °C) 的阻值漂移为 0.04 %。

自热系数

0.4 K/mW 在 0 °C

绝缘阻抗

> 100 MΩ 在 20 °C

> 2 MΩ 在 500 °C

抗振动性

根据安装情况, 在10至2000 Hz的频率下, 加速度至少为40 g

抗冲击特性

根据安装情况, 至少带有8 ms半正弦波的100 g加速度

连接技术

压接, 熔焊, 钎焊

引脚材质

镍镀铂引线

引脚拉力

≥ 6N

包装

真空塑料包装

按要求提供其他包装形式

保质期

未开封状态下至少可储存12个月

备注

其他公差, 电阻值和电线长度可根据要求提供。

由于随机取样测量, 可能会发生连接线弯曲 (称为V形)。这种弯曲是与批次相关的, 对铂测量电阻的功能没有影响。

RoHS
compliant

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under www.yageo-nexensos.com/tc or may be furnished upon request. This data sheet is subject to changes without prior notice.

YAGEO Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany

Document: 20005739626 | Part 002 | Version 01 | Status: 11/2024

YAGEO Nexensos GmbH, Germany
网址: www.yageo-nexensos.cn
联系方式: nexensos.china@yageo.com

2页中的第 2