

## TH系列 - 螺纹型铂温度传感器


温度范围 -40 °C至 +250 °C

### 性能特征

- 优异的导热性
- 可靠的传感器固定
- 易于安装
- 符合DIN EN IEC 60751

### 应用示例

- 暖通空调
- 母线系统
- 散热器
- 电机和轴承箱



图片仅供参考

### 尺寸和材料

编号	产品类型	芯片电阻 R <sub>0</sub> [Ω]	尺寸和公差 (mm)						导线			产品料号
			螺纹类型	TL	HL	WS	CL	L	线芯 (AWG)	绝缘	颜色	
1	TH16G1/8-T8	Pt100 / F 0.3	G1/8	8 ±0.2	16 ±0.2	13 ±0.2	200 ±10	196 ±10	26/01 Ni	PTFE	白色	30010007
2	TH16G1/8-T8	Pt1000 / F 0.3	G1/8	8 ±0.2	16 ±0.2	13 ±0.2	200 ±10	196 ±10	26/01 Ni	PTFE	白色	30010000

## TH系列 - 螺纹型铂温度传感器

温度范围 -40 °C至 +250 °C

### 性能数据

编号	温度范围	外壳材料	介电强度AC (外壳)	响应时间 水流 (v = 0.4 m/s)		拉力 [N]	导体电阻 [Ω/m]	应用
				T0.5 [s]	T0.9 [s]			
1	-40 °C 至 +250 °C	2.0401 Brass	500 V, 10 s	3.8	4.9	> 85	0.69 ±10 %	多用途
2	-40 °C 至 +250 °C	2.0401 Brass	500 V, 10 s	3.8	4.9	> 85	0.69 ±10 %	多用途

### 温度系数

TCR = 3850 ppm/K

### 工作电流

Pt100 Ω: 0.3 至 1.0 mA

Pt1000 Ω: 0.1 至 0.3 mA

(必须考虑自加热)

### 自热系数 (元件)

0 °C 下 0.4K/mW

### 自定义选项

- 所有外部尺寸
- 导线尺寸和材质
- 传感器电阻值
- 连接器
- 认证 (如IMDS、PPAP、IP防水等级)

如需了解更多信息，  
请浏览我们的传感器学  
院！



RoHS  
compliant

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under [www.yageo-nexensos.com/tc](http://www.yageo-nexensos.com/tc) or may be furnished upon request. This data sheet is subject to changes without prior notice.

YAGEO Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany

YAGEO Nexensos GmbH, Germany

网址: [www.yageo-nexensos.cn](http://www.yageo-nexensos.cn)

邮箱: [nexensos.china@yageo.com](mailto:nexensos.china@yageo.com)

Document: 20003959429 Part 002 Version 04 | Status: 11/2024

2页中的第2