

SOT223, Housed Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -50 °C to +150 °C

- Platinum sensor precision in SOT223 format
- Excellent long term stability
- High accuracy
- High vibration and shock resistance
- Optimized for soldering

The SOT223 is a Pt-RTD enclosed in an industry-standard SOT housing and is characterized by a linear resistance v. temperature response (as per DIN EN IEC 60751), interchangeability, high long-term stability and accuracy. Designed for easy mounting in electronic assemblies and ideal for temperature compensation on PCBs, the SOT223 sensor is equipped with a cooling fin to enhance thermal contact with the PCB.

Nominal Resistance R_0 [Ω]	Tolerance Class	Order Number	Packaging
Pt1000	F 0.6 (2B)	32209116	Blister reel

Temperature Range of Tolerance Class

Validity of Class F 0.6 (2B) -50 °C to +150 °C

The specified tolerance classes refer to continuous operation.

Temperature Coefficient

TCR = 3850 ppm/K

Response Time

Water ($v = 0.4$ m/s):
 $t_{0.5} = 0.45$ s
 $t_{0.9} = 1.2$ s

Air ($v = 2$ m/s):
 $t_{0.5} = 8$ s
 $t_{0.9} = 26$ s

Measuring Current

Pt1000 Ω: 0.1 to 0.3 mA
 (self-heating has to be considered)

Long-Term Stability

The drift of the resistance value at 0 °C after a storage for 1000 hours in air at the declared upper temperature limit is not more than the tolerance value of the declared tolerance class according DIN EN IEC 60751. Typical drift of $R(0$ °C) is 0.06 % after 1000 hours at +150 °C.

Self-Heating

0.049 K/mW at 0 °C mounted on PCB
 0.2 K/mW at 0 °C package only

Specific Volume Resistance

100 °C = 14×10^{14} Ωcm
 150 °C = 0.3×10^{12} Ωcm

Physical Data For Housing

Material: duroplastic
 Coefficient of thermal expansion: 12×10^{-6} 1 /K (below T_g)
 Thermal Conductivity: 1.04 W/mK
 Moisture absorption: Boiling water (48 hours) < 1.0 %
 YAGEO Nexensos GmbH, Germany
 Web: www.yageo-nexensos.com
 Contact: nexensos.america@yageo.com




Image for illustration purposes only
 The wide connection lug is used for heat transfer

SOT223, Housed Pt Temperature Sensor according to DIN EN IEC 60751

Temperature range -50 °C to +150 °C

Flammability

UL94-V0

Soldering Connection

Cu alloy with Sn coating

Connection Technology

Soft Soldering

Packaging

Blister reel

Alternative packaging forms on request

Storage Life

9 months (in original packaging).

Nitrogen atmosphere recommended

Note

Other tolerances and values of resistance are available on request

California Proposition 65



WARNING

WARNING: This product can expose you to chemicals including carbon black, which is known to the State of California to cause cancer.

For more information go to www.p65warnings.ca.gov

RoHS
compliant

The information provided in this data sheet describes certain technical characteristics of the product, but shall not be qualified or construed as quality guarantee (Beschaffenheitsgarantie) in the meaning of sections 443 and 444 German Civil Code. The information provided in this data sheet regarding measurement values (including, but not limited to, response time, long-term stability, vibration and shock resistance, insulation resistance and self-heating) are average values that have been obtained under laboratory conditions in tests of large numbers of the product. Product results or measurements achieved by customer or any other person in any production, test, or other environment may vary depending on the specific conditions of use. YAGEO Nexensos does not recommend the use of standard catalogue products or automotive grades for aerospace applications or manned space flight. The customer is solely responsible to determine whether the product is suited for the customer's intended use; in this respect YAGEO Nexensos cannot assume any liability. The sale of any products by YAGEO Nexensos is exclusively subject to the General Terms of Sale and Delivery of YAGEO Nexensos in their current version at the time of purchase, which is available under www.yageo-nexensos.com/tc or may be furnished upon request. This data sheet is subject to changes without prior notice.

YAGEO Nexensos GmbH, Reinhard-Heraeus-Ring 23, 63801 Kleinostheim, Germany

YAGEO Nexensos GmbH, Germany
Web: www.yageo-nexensos.com
Contact: nexensos.america@yageo.com

Document: 20002221298 | Part 001 | Version 03 | Status: 11/2024

Page 2 of 2